

## DATA SHEET

REF. HANDRY-2 Negro, HANDRY-2 Blanco,  
HANDRY-2 Amarillo, HANDRY-2 Verde,  
HANDRY-2 Rojo, HANDRY-2 Azul



## HAND DRYER PROANJET

**PROANDRE**  
HYGIENE SOLUTIONS

### GENERAL

**WARRANTY:** 5 years or 200.000 cycles.

**ACTUATION METHOD:** It activates when detecting hands by an infrared led.

### AMBIENCE

**TEMPERATURE RANGE:** 5 / 40°C.

**HUMIDITY RANGE:** 20-90%.

### HAND DRYER PROANJET

**MOUNTING:** Screw to the wall.

**NET WEIGHT:** 7,7Kg.

**GROSS WEIGHT:** 9,2Kg.

**DIMENSIONS:** 66 x 34 x 24cm / 25. 98 x 13. 38 x 9. 44 inch.

**MATERIAL:** Plástico ABS.

**COLOR:** White / Black / Blue / Red / Green / Yellow.

**FILTER:** HEPA 13.

**MOTOR:** Universal.

**MARKETING:** Can be customized with logo.

### ELECTRONICS

**POWER SOURCE:** 220-240V-110-120V.

**POWER:** 1100W.

**WORKING CURRENT:** 5A-9A.

### HOW TO USE


1. Insert your hands in the drying area to activate the operation and the air outlet. Leave your hands in the drying area until the cycle ends.
2. Cleaning device (Surfaces): Make sure that all the surfaces are cleaned directly with a damp cloth, without abrasive or caustic products.

· **Maintenance Tips:** Control mode regulates the entry of air through the Handry's base and make sure it is free of dust, debris and other particles. Also, make sure that all surfaces are properly cleaned to maintain an uninterrupted operation.


· **Test:** Make sure the device is connected. Insert your hands in the drying area to activate its operation and the air outlet. When removing hands, the device will stop automatically.

### FEATURES

Lateral activation. Thanks to its capacitive sensor allows the start-up of the dryer by entering the hands through any cavity. Antibacterial additive. All units incorporate a HEPA 13 filter. Recommended in environments with high standards of disinfection and hygiene. All plastic components incorporate an antibacterial additive. All plastic components incorporate an antibacterial additive. It is recommended to change the filter every 50,000 cycles approximately. Led Diagnostics: Discreet silent alarm system that facilitates maintenance of the unit, indicating full water tank, or technical failure. Telemetry system via Bluetooth: Thanks to its developed App and using Bluetooth technology, access to the statistics of use of the unit is easy. It is not necessary to disassemble the dryer to obtain the data. Easy access to internal components.



Register No.: AN-04-DM-01  
Version: 003  
Date: 06 / 04 / 2022



HAND DRYER ON PALLETS